







FRONT VIEW




BOTTOM VIEW



RECOMMENDED P.C.B. LAYOUT
(COMPONENT SIDE OF BOARD)




SIDE VIEW




FRONT VIEW
RECOMMENDED PANEL CUTOUT



REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	ECN E07169	MAY 30/07	L.CHAN
B	ADD DIMENSION	AUG 03/16	L.CHAN
C	ADD PANEL INFORMATION AND CONTACT WIDTH	DEC 06/16	L.CHAN
D	ADD RECOMMENDED PCB THICKNESS	DEC 08/16	L.CHAN



DETAIL Y



SIDE VIEW SHOWING
WITH PANEL AND PCB

MATERIALS:

HOUSING: ENGINEERING THERMOPLASTIC,
BLACK COLOR, FLAMMABILITY RATING UL 94V-0.

CONTACTS: 0.35MM THICK PHOSPHOR BRONZE
PLATED WITH HARD GOLD (SEE PART NO. CODE FOR THICKNESS) AND
GOLD FLASH IN SOLDER AREA.

SHIELD: 0.25MM THICK COPPER ALLOY
PLATED WITH NICKEL

AMPHENOL PARTNUMBER: RJE30-488-1X10

GOLD PLATING

- 1 = 6 u"
- 2 = 15 u"
- 3 = 30 u"
- 4 = 50 u"

UNLESS SPECIFIED OTHERWISE	DRAWN LUO W W	DATE MAY30/07
PRIMARY UNITS INCH	CHECKED L.CHAN	MAY30/07
SECONDARY MILLIMETER	M.E. APP'D	
REFERENCE IN PARENTHESES	Q.A. APP'D	
GENERAL TOLERANCES	DWG APPR.	
1 DECIMAL PLACE ±0.025	ENG. REL. NO.	
2 DECIMAL PLACES ±0.020	REF.	
3 DECIMAL PLACES ±0.015	THIRD ANGLE PROJECTION	DO NOT SCALE DRAWING
ANGULAR DEGREES ±1.0°		

Amphenol Canada Corp.		www.amphenolcanada.com	
TITLE		STACKABLE MODULAR JACK, 2X2 PORT,SHIELD,8 POSITIONS,8 CONTACTS -RoHS COMPLIANT	
DWG. NO.		P-RJE30-488-1X10	
CODE ID NO. 03554		DWG SIZE: C SCALE: N/A SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RJE304881310](#)