






REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-8B0411~414	2015/09/22	Shin	Add Note
C	LEN1590291~297	2015/09/07	Vicky	Update Logo & Note
D	LEN1650559~565	2016/05/17	Ruru	Modify Logo Position



12	Light Green	淺綠
11	Purple	紫
10	Orange	橙
9	Black	黑
8	Red	紅
7	Pink	粉紅
6	Gray	灰
5	Yellow	黃
4	Green	綠
3	White	白
2	Blue	藍
1	Brown	棕
Conn.	Wire Color	
	Pin Out	

Note:

- * $\varnothing$ Important Dimensions To Check
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black
- * Male Pin: Copper Alloy, Gold Plated
- * Cable: UL2464 26#*12C+D+Al/My,UV, PVC Jacket, Black, OD=6.0mm
- * $\triangle B$ Use with waterproof cap or dust cap
Panel Thickness Max: 2.5mm
- * $\triangle B$ Use without waterproof cap or dust cap
Panel Thickness Max: 3.5mm
- * $\triangle C$ Cable Length Tolerance: 1M:±40mm
2M~5M:±60mm
6M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm				TITLE		Standard		Amphenol LTW		ITEM NO		DRAWN BY		DATE			
TOLERANCE ±0.5 mm				Cable Lock 12Pin M Conn M Pin						DWG NO		CHECKED BY		DATE			
				SCALE 3:2		SIZE A4				SHEET 1 OF 1		BU-12PMMM-LL7AXX		Rita		2016-05-17	
				REV. D		WC-REV. A.1				QC: Inspection item		CUSTOMER		APPROVED BY		DATE	
								安費諾亮泰企業股份有限公司		ALTW		Lisa		2016-05-17			
1		2		3		4		5		6		7		8 FMM10702-01-02A			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BU-12PMMM-LL7A02](#) [BU-12PMMM-LL7A05](#) [BU-12PMMM-LL7A10](#) [BU-12PMMM-LL7A01](#)