



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.


REV.	ECN NO.	DATE	SIGN	DESCRIPTION



CD-09AFMM-QL8DXX

XX : 01~99Meters
01 : 01Meter
02 : 02Meters
:
:
99 : 99Meters

- Note:
- * Important Dimension To Check.
 - * Working Voltage Rating: AC 300V
 - * Working Current Rating: 5A
 - * Flame Class: UL94V-0 (UV Resistance)
 - * Waterproof Rate: IP68. (Mated)
 - * Housing: Nylon+GF, Black
 - * Male Pin: Copper Alloy, Gold Plated
 - * Cable: UL21388 20AWG*9C+AL.Mylar Black, PVC Jacket UV Resistant, OD=7.6
 - * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm



Pin Assignments
Front View

9	Gray	灰
8	Purple	紫
7	Blue	藍
6	Green	綠
5	Yellow	黃
4	Orange	橙
3	Red	紅
2	Brown	棕
1	Black	黑
Conn.	Wire Color	
Pin Out		

UNIT:mm		TOLERANCE ±0.5		TITLE X Lok C-Size Cable 9 Pin 5A F Conn. M Pin		ITEM NO		DRAWN BY Micky		DATE 2014-12-12	
SCALE 1:1		SIZE A4		SHEET 1 OF 1		DWG NO CD-09AFMM-QL8DXX		CHECKED BY Spring		DATE 2014-12-12	
REV. A		WC-REV. A.1		QC: Inspection item		CUSTOMER ALTW		APPROVED BY Kevin		DATE 2014-12-12	

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CD-09AFMM-QL8D03](#) [CD-09AFMM-QL8D10](#) [CD-09AFMM-QL8D04](#) [CD-09AFMM-QL8D02](#) [CD-09AFMM-QL8D01](#)
[CD-09AFMM-QL8D05](#)