



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.


1	2	3	4	5	6	7	8
REV.	ECN NO.	DATE	SIGN	DESCRIPTION			



Conn.

CD-07AFMM-QL8W00
Color: Black


White Printing
白色印刷



CD-07AFMM-QL8DXX

XX : 01~99Meters
01 : 01Meter
02 : 02Meters
:
:
99 : 99Meters

- Note:
- * Important Dimension To Check.
 - * Working Voltage Rating: AC 300V
 - * Working Current Rating: 5A
 - * Flame Class: UL94V-0 (UV Resistance)
 - * Waterproof Rate: IP68(Mated)
 - * Housing: Nylon+GF,Black
 - * Male Pin: Copper Alloy, Gold Plated
 - * Cable: UL21388 20AWG*7C+AL/PET Tape
Black, PVC Jacket UV Resistant, OD=6.8
 - * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm



Pin Assignments
Front View

7	Orange	橙
6	Blue	藍
5	Purple	紫
4	Yellow	黃
3	Black	黑
2	Red	紅
1	White	白
Conn.	Wire Color	
	Pin Out	

UNIT:mm	
TOLERANCE	±0.5

TITLE X Lok C-Size Cable 7 Pin 5A F Conn. M Pin			
SCALE 1:1	SIZE A4	SHEET 1 OF 1	
REV. A	WC-REV. A.1	QC: Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Micky	DATE 2014-12-12
DWG NO CD-07AFMM-QL8DXX	CHECKED BY Spring	DATE 2014-12-12
CUSTOMER ALTW	APPROVED BY Kevin	DATE 2014-12-12

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CD-07AFMM-QL8D04](#) [CD-07AFMM-QL8D01](#) [CD-07AFMM-QL8D03](#) [CD-07AFMM-QL8D05](#) [CD-07AFMM-QL8D10](#)
[CD-07AFMM-QL8D02](#)