






THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-8B0530-533	2008/09/22	Shin	Add Note
C	LEN1590284-287	2015/09/03	Vicky	Update Logo & Note
D	LEN1640089-092	2016/04/08	Vicky	Modify Logo Position



XX: 01~99Meters
01: 01Meter
02: 02Meters
...
99: 99Meters
Cable Length(L): 01~99Meters

- Note:
- * CC Important Dimensions To Check
 - * Waterproof Rate: IP67
 - * Housing: Nylon+GF, Black
 - * Male Pin: Copper Alloy, Gold Plated
 - * Cable: UL2464 26#*10C+D+Al/My,UV, PVC Jacket, Black, OD=6.0mm
 - * $\triangle B$ Use with waterproof cap or dust cap
Panel Thickness Max: 2.5mm
 - * $\triangle B$ Use without waterproof cap or dust cap
Panel Thickness Max: 3.5mm
 - * $\triangle C$ Cable Length Tolerance: 1M: ± 40 mm
2M~5M: ± 60 mm
6M~10M: ± 100 mm
11M~30M: ± 200 mm
31M~99M: ± 500 mm



10	Orange	橙
9	Black	黑
8	Red	紅
7	Pink	粉紅
6	Gray	灰
5	Yellow	黃
4	Green	綠
3	White	白
2	Blue	藍
1	Brown	棕
Conn.	Wire Color	
	Pin Out	

Pin Assignments
Front View

Recommended Panel Cut-Out

UNIT:mm		TOLERANCE		TITLE		ITEM NO		DRAWN BY		DATE	
± 0.5 mm				Standard Cable Screw 10Pin M Conn M Pin		BU-10PMMM-SL7AXX		Vicky		2016-04-08	
				SCALE: 3:2		DWG NO		Rita		2016-04-08	
				REV. D		CUSTOMER		Lion		2016-04-08	
				WC-REV. A.1		ALTW					
				CC : Inspection item							

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BU-10PMMM-SL7A02](#) [BU-10PMMM-SL7A05](#) [BU-10PMMM-SL7A01](#) [BU-10PMMM-SL7A10](#)