






THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-8B0536-539	2008/09/10	Shin	Add Note
C	LEN1590299-303	2015/09/07	Vicky	Update Logo & Note
D	LEN1640094-098	2016/04/08	Vicky	Modify Logo Position



12	Light Green	淺綠
11	Purple	紫
10	Orange	橙
9	Black	黑
8	Red	紅
7	Pink	粉紅
6	Gray	灰
5	Yellow	黃
4	Green	綠
3	White	白
2	Blue	藍
1	Brown	棕
Conn.	Wire Color Pin Out	

Note:

- * CC Important Dimensions To Check
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black
- * Male Pin: Copper Alloy, Gold Plated
- * Cable: UL2464 26#*12C+D+Al/My,UV, PVC Jacket, Black, OD=6.0mm
- * B Use with waterproof cap or dust cap
Panel Thickness Max: 2.5mm
- * B Use without waterproof cap or dust cap
Panel Thickness Max: 3.5mm
- * C Cable Length Tolerance: 1M:±40mm
2M~5M:±60mm
6M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm		TITLE	Standard
TOLERANCE	±0.5 mm	Cable Screw 12Pin M Conn M Pin	
SCALE	3:2	SIZE	A4
REV.	D	WC-REV.	A.1
		CC	Inspection item

ITEM NO	DWG NO	CUSTOMER	DRAWN BY	CHECKED BY	APPROVED BY	DATE
	BU-12PMMM-SL7AXX	ALTW	Vicky	Rita	Lion	2016-04-08
						2016-04-08
						2016-04-08

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BU-12PMMM-SL7A02](#) [BU-12PMMM-SL7A01](#) [BU-12PMMM-SL7A05](#) [BU-12PMMM-SL7A10](#)