




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION



Pin Assignments
Front View

7	Blue	藍
6	Green	綠
5	Yellow	黃
4	Orange	橙
3	Red	紅
2	Brown	棕
1	Black	黑
Conn.	Wire Color	
Pin Out		

CD-07AFMM-QR8DXX

XX :01~99Meters
01 :01Meter
02 :02Meters
:
:
99 :99Meters

- Note:
- * QC Important Dimension To Check.
 - * Working Voltage Rating: AC 300 V
 - * Working Current Rating: 5A
 - * Flame Class: UL94V-0 (UV Resistance)
 - * Waterproof Rate: IP68(Mated).
 - * Housing: Nylon+GF, Black.
 - * Male Pin: Copper Alloy, Gold Plated
 - * Cable: UL21388 20AWG*8C+AL.Mylar Black,PVC Jacket UV Resistant, OD=6.8
 - * Cable Length Tolerance:01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm		TOLERANCE ±0.5		TITLE X Lok C-Size 90° Cable 7 Pin 5A F Conn. M Pin		ITEM NO		DRAWN BY Micky		DATE 2014-12-12	
SCALE 1:1		SIZE A4		SHEET 1 OF 1		DWG NO CD-07AFMM-QR8DXX		CHECKED BY Spring		DATE 2014-12-12	
REV. A		WC-REV. A.1		<u>QC</u> :Inspection item		CUSTOMER ALTW		APPROVED BY Kevin		DATE 2014-12-12	
1		2		3		4 比例 3:2		5		6	
										7	
										8 FMW10702-01-02A1	

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CD-07AFMM-QR8D02](#) [CD-07AFMM-QR8D10](#) [CD-07AFMM-QR8D05](#) [CD-07AFMM-QR8D03](#) [CD-07AFMM-QR8D01](#)
[CD-07AFMM-QR8D04](#)