







REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-9A0255~258	2009/04/17	Li Xiu Zhi	Change SR View & Update Note
C	LEN1480096~099	2014/07/29	Vicky	Update Logo



Conn.



Pin Assignments
Front View

8	Green	20AWG	綠
7	Blue	20AWG	藍
6	Yellow	24AWG	黃
5	Orange	24AWG	橘
4	Red	24AWG	紅
3	Brown	24AWG	棕
2	Black	24AWG	黑
1	Purple	24AWG	紫
Conn.	Wire Color		
Pin Out			

CBD-08AFFM-SL7AXX

XX :01~99Meters
01 :01Meter
02 :02Meters
:
99 :99Meters

Cable Length(L):01~99Meters

Note:

- * Important Dimension To Check
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black
- * Female Pin: Copper Alloy, Gold Plated
- * Screw Nut: Nylon+GF, Black
- * O-Ring: EPDM, Black
- * Cable: UL2464 (20AWG*2C+24AWG*6C)+Drain+Al/My, Black,PVC Jacket,UV Resistant,OD=6.0
- * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm
TOLERANCE
±0.5 mm

TITLE Middle Cable Screw 8Pin F Conn F Pin			
SCALE 1:1	SIZE A4	SHEET 1 OF 1	
REV. C	WC-REV. A.1	QC: Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Vicky	DATE 2014-07-29
DWG NO CBD-08AFFM-SL7AXX	CHECKED BY Sam	DATE 2014-07-29
CUSTOMER ALTW	APPROVED BY Rita	DATE 2014-07-29

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CBD-08AFFM-SL7A02](#) [CBD-08AFFM-SL7A05](#) [CBD-08AFFM-SL7A10](#) [CBD-08AFFM-SL7A01](#)