



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION



① CD-08AFFM-QR8W00
Color: Black

QC White Printing
白色印刷





Conn.

Note:

- * QC Important Dimension To Check.
- * Working Voltage Rating: AC 300 V
- * Working Current Rating: 5A
- * Flame Class: UL94V-0 (UV Resistance)
- * Waterproof Rate: IP68(Mated).
- * Housing: Nylon+GF, Black.
- * Female Pin: Copper Alloy, Gold Plated
- * Cable: UL21388 20AWG*8C+AL Mylar Black,PVC Jacket UV Resistant, OD=7.2
- * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

CD-08AFFM-QR8DXX

XX :01~99Meters
01 :01Meter
02 :02Meters
:
:
99 :99Meters



Pin Assignments
Front View

8	Purple	紫
7	Blue	藍
6	Green	綠
5	Yellow	黃
4	Orange	橙
3	Red	紅
2	Brown	棕
1	Black	黑
Conn.	Wire Color	
Pin Out		

UNIT:mm	
TOLERANCE	±0.5

TITLE X Lok C-Size 90° Cable 8 Pin 5A F Conn. F Pin			
SCALE 1:1	SIZE A4	SHEET 1 OF 1	
REV. A	WC-REV. A.1	QC:Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Micky	DATE 2014-12-11
DWG NO CD-08AFFM-QR8DXX	CHECKED BY Spring	DATE 2014-12-11
CUSTOMER ALTW	APPROVED BY Kevin	DATE 2014-12-11

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CD-08AFFM-QR8D04](#) [CD-08AFFM-QR8D02](#) [CD-08AFFM-QR8D01](#) [CD-08AFFM-QR8D03](#) [CD-08AFFM-QR8D05](#)
[CD-08AFFM-QR8D10](#)