





THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LE31180043 ~046	2011/08/12	Jiang Jun Hua	Change Drawings
C	LENI590395~98	2015/09/11	Ruru	Change Logo
D	LE315C0382~385	2015/12/11	Ruru	Change Ball-marker & Tolerance




BU-10BMMM-LL7AXX

XX: 01~99Meter
01: 01Meter
02: 02Meters
:
:
:
99: 99Meters

Cable Length(L): 01~99Meters

Note:

- * Important Dimension To Check.
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black
- * Pin: Copper Alloy, Gold Plated
- * Cable: UL2464 26AWG*10C+Drain+Al/My, PVC Jacket UV Resistant, OD=6.0, Black
- * Cable Length Tolerance: 01M: ±40mm
02M~05M: ±60mm
06M~10M: ±100mm
11M~30M: ±200mm
31M~99M: ±500mm



PIN ASSIGNMENTS
Front View前視圖

Orange	橙	10
Black	黑	9
Red	紅	8
Pink	粉紅	7
Gray	灰	6
Yellow	黃	5
Green	綠	4
White	白	3
Blue	藍	2
Brown	棕	1
Wire Color	Conn.	
Pin Out		

UNIT: mm		TITLE	STANDARD
TOLERANCE	± 0.5mm	CABLE LOCK 10PIN M CONN M PIN	
SCALE	1:1	SIZE	A4
REV.	D	WC-REV.	A.2
		SHEET	1 OF 1
		QC	Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	Ruru	2015-12-11
CUSTOMER	CHECKED BY	DATE
ALTW	Rtia	2015-12-11
	APPROVED BY	DATE
	Lisa	2015-12-11

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BU-10BMMM-LL7A03](#)