





THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A	Initial Release	2016-05-07	Spring	Change Rev.02 To Rev.A



Conn.



Conn.
Pin Assignments
Front View

6	Blue (26AWG)	藍	Twist 對線
5	Red (26AWG)	紅	
4	Green (26AWG)	綠	Twist 對線
3	White (26AWG)	白	
2	Black (16AWG)	黑	
1	White (16AWG)	白	
Conn.	Wire Color		
Pin Out			

BBD-06AMFM-QL8FXX

XX:01~99Meters
01:01Meter
02:01Meters
:
99:99Meters
Cable Length(L):01~99Meters

Note:
* $\varnothing$ Important Dimension To Check.
* Waterproof Rate: IP68(Mated)
In 1 meter water within 24 hours
* Working Voltage Rating:
Power: AC/DC 300V
Data: DC 30V
* Working Current:
Power: 10A
Data: 05A
* Housing: Nylon+GF, Black.
* Pin: Copper Alloy, Gold Plated.
* Cable: UL21996 16AWG*2C+(26AWG*2P+AL/MY)
+F+AL/MY, PVC Jacket, OD=9.3, Black.
* Cable Length Tolerance: 01M: ±40mm
02M~05M: ±60mm
06M~10M: ±100mm
11M~30M: ±200mm
31M~99M: ±500mm

UNIT:mm	
TOLERANCE	±0.5mm

TITLE CIRCULAR,STANDARD,CABLE X-LOK (2+4)PIN M CONN F PIN			
SCALE 3:2	SIZE A4	SHEET 1 OF 1	
REV. A	WC-REV. A.1	$\varnothing$ Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Spring	DATE 2016-05-07
DWG NO BBD-06AMFM-QL8FXX	CHECKED BY Fisher	DATE 2016-05-07
CUSTOMER ALTW	APPROVED BY Kevin	DATE 2016-05-07

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BBD-06AMFM-QL8F05](#) [BBD-06AMFM-QL8F10](#) [BBD-06AMFM-QL8F02](#) [BBD-06AMFM-QL8F04](#) [BBD-06AMFM-QL8F03](#)