





DIM	Ø2.0			Ø2.5
SCHEMATIC				

6	HOUSING	PBT (RATED UL 94V-0)		1
5	COVER	PA		1
4	CENTER PIN	BRASS	NICKEL PLATED	1
3	TERMINAL NO. 3	PHOSPHOR BRONZE	TIN PLATED	1
2	TERMINAL NO. 2	BRASS	TIN PLATED	1
1	TERMINAL NO. 1	BRASS	TIN PLATED	1
ITEM	NAME	MATERIAL	FINISH	SUM



P.C.B. LAYOUT
BOTTOM VIEW

NOTE:

- 1.PART NUMBER WITH "LF" SUFFIX FULLY COMPLY WITH THE DEFINITIONS GIVEN IN DIRECTIVE 2002/95/EC OF EUROPEAN PARLIAMENT.
- 2.FOR "LF" SUFFIX ITEMS RoHS LOGO LABEL TO BE PROVIDED ON THE PACKING BOX.

10080805-002/10080805-002LF	2.5mm
10080805-001/10080805-001LF	2.0mm
PART NUMBER	PIN Ø

mat'l. code REF TABLE				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection MM	product family MOD JACK
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
					angles	linear	DC POWER JACK
					0°±3°	linear	
					dr	HIRAN	2007/07/25
					engr	HIRAN	2007/07/25
					chr	HIRAN	2007/07/25
					appd	HIRAN	2007/07/25
A	107-0092	HVN	2007/07/25	appd	HIRAN	2007/07/25	FCJ
sheet	revision	A					dwg no
index	sheet	1					10080805
							type
							Product Customer Drawing

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[10080805-002LF](#)