







REV.	DATE	DESCRIPTION
A	06/03/99	ADD 50ohm TO DESCRIPTION



DESCRIPTION	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS FOR CUSTOMER REFERENCE ONLY	APPROVALS	DATE	TITLE	SCALE	PART NO.	SHEET		
1 BODY	BRASS	NICKEL	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS FOR CUSTOMER REFERENCE ONLY UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5-6 = ± 0.2 6-30 = ± 0.4 30-120 = ± 0.6 120-315 = ± 1 315-1000 = ± 1.6 1000-2000 = ± 2.4	DRAWN	G.R.S.	06/03/99	comnex Connector Corporation BNC BULKHEAD FRONT MOUNT DIRECT SOLDER JACK - 50ohm (FOR .085", .086" CABLE)	NA	112609	1	OF 1
2 BARREL	BRASS	GOLD		CHECKED							
3 INSULATOR	TEFLON	NATURAL		ISSUED							
4 CONTACT PIN	PHOS. BRONZE	GOLD									
5 LOCK WASHER	BRASS	NICKEL									
6 HEX NUT	BRASS	NICKEL									
7											
8				DO NOT SCALE DRAWING							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[112609](#)