



REV.	DATE	DESCRIPTION
A	08/08/02	UPDATE BARREL DIAMETER



CRIMP NOTES:  
 1) CRIMP FERRULE  
 HEX CRIMP SIZE .178"  
 2) CONTACT PIN TO SOLDER

DESCRIPTION	MATERIAL	FINISH	DO NOT SCALE DRAWING	APPROVALS	DATE	TITLE	SCALE	PART NO.	DWG. NO.	REV.	
8			UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS	DRAWN G.R.S.	08/08/02	SMB R/A POSITION LOCK CRIMP PLUG (FOR RG-180B/U, 195/U CABLE)	A	99001	142292	A	
7			DIMENSIONS IN [ ] ARE IN INCHES FOR CUSTOMER REFERENCE ONLY								CHECKED
6			UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .XXX = ± 0.005" .XX = ± 0.010" .X = ± 0.020"								ISSUED
5	FERRULE	BRASS	NICKEL								
4	RETAINER RING	BER. COPPER	NATURAL								
3	CONTACT PIN	BER. COPPER	GOLD								
2	INSULATOR	TEFLON	NATURAL								
1	BODY/SHELL	BRASS	NICKEL								

**Amphenol - Connex**  
 CONNECTOR CORPORATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[142292](#)