


REV.	DATE	DESCRIPTION
A	03/27/05	UPDATE DRAWING FORMAT
B	07/17/07	REVISE OVERALL LENGTH, BACK END CONFIGURATION



8					<div>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.</div> <div>UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm</div> <div>UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"</div> <div>DO NOT SCALE DRAWING</div>	APPROVALS	DATE	<h1>Amphenol Connex</h1>						
7						DRAWN	G.R.S.							07/17/07
6						CHECKED			PART DESCRIPTION SMA PLUG TO MMCX JACK					
5	GASKET	SILICONE	RED	1		ISSUED								
4	RETAINER RING	BER. COPPER	GOLD	1		SHEET	1 OF 1							
3	CONTACT PIN	BER. COPPER	GOLD	1					PART NO. 242140					
2	INSULATOR	TEFLON	NATURAL	1										
1	BODY	BRASS	GOLD	1				DWG. NO. 242140.DWG REV. B SIZE A SCALE NA						
	DESCRIPTION	MATERIAL	FINISH	QTY	C:/242/242140.DWG									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[242140](#)