



1. MATERIALS AND FINISHES:
BODY & COUPLING NUT - BRASS, NICKEL PLATING
CONTACT - BERYLLIUM COPPER, GOLD PLATING
INSULATOR - PTFE
GASKET - RUBBER
2. ELECTRICAL:
A. IMPEDANCE: 75 OHM
B. FREQUENCY RANGE: DC - 4 GHz
C. RETURN LOSS: 28 dB MIN.
3. MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: -65° C TO +165° C
4. PACKAGING:
A. QUANTITY: SINGLE PACK
B. MARKING: BAG TO BE MARKED
"AMPHENOLRF, APH-BNCP-HDBNCJ, AND DATE CODE"

REVISIONS

| | | | | |
|-----|-----------------|--------|-------|------|
| REV | DESCRIPTION | DATE | ECO | APPR |
| A | RELEASE TO MFG. | 8/3/10 | 48170 | CL |



SCALE 2.000



CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

| | | | | | | | |
|--|-----------------------------------|--|---|--|---|-------------------------------------|--|
| <div>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm 0.5 - 6mm 6 - 30mm 30 - 120mm ANGLES ± 0.05mm ±0.1mm ±0.2mm ± 0.3mm ±1°</div> <div>NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.</div> | <div>MATERIAL SEE NOTES</div> | <div>DRAWN S.LI</div> | <div>DATE 07-Jul-10</div> | <div>TITLE BNC PLUG TO HD-BNC JACK, 75 OHM ADAPTER</div> | <div>Amphenol RF Danbury CT USA, Tainan, Taiwan, Shenzhen, China www.amphenolrf.com</div> | | |
| | | <div>ENGINEER CLEMENT</div> | <div>DATE 29-Mar-10</div> | | | | |
| | | <div>REFERENCE EAR #</div> | <div>DATE 18-Oct-10</div> | | | | |
| | | <div>CONFIGURATION LEVEL: =%%Z0HXIBGC=</div> | <div>APPROVED S.HSIEH</div> | <div>SCALE: 4.0:1.0</div> | | <div>SHEET 2 OF 2</div> | <div>DRAWING NO. APH-BNCP-HDBNCJ</div> |
| | | <div>FINISH</div> | <div>CAD FILE Root Folder/BNC/APH-BNCP-HDBNCJ</div> | <div>DWG SIZE B</div> | <div>REV A</div> | <div>ITEM NO. APH-BNCP-HDBNCJ</div> | <div>PART NO. APH-BNCP-HDBNCJ</div> |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[APH-BNCP-HDBNCJ](#)