





| REV. | DATE     | ECR NO. | DESCRIPTION     |
|------|----------|---------|-----------------|
| NC   | 05/14/09 | –       | INITIAL RELEASE |



RECOMMENDED  
CABLE STRIPPING DIM'S



NOTE:

1. CRIMPED FERRULE  
HEX CRIMP SIZE .255"
2. CRIMPED CONTACT PIN  
HEX CRIMP SIZE .068"

|    |                   |                 |         |     |
|----|-------------------|-----------------|---------|-----|
| 14 | FERRULE           | BRASS           | NICKEL  | 1   |
| 13 | CONTACT PIN       | BRASS           | GOLD    | 1   |
| 12 | COVER             | BRASS           | NICKEL  | 1   |
| 11 | CONTACT PIN       | BRASS           | GOLD    | 1   |
| 10 | WASHER            | BRASS           | NICKEL  | 1   |
| 9  | RING              | DELTRIN         | NATURAL | 1   |
| 8  | RETAINER RING     | BRASS           | NICKEL  | 1   |
| 7  | GASKET            | RUBBER          | RED     | 1   |
| 6  | INSULATOR         | DELTRIN         | NATURAL | 1   |
| 5  | BARREL            | BRASS           | NICKEL  | 1   |
| 4  | CONTACT PIN       | PHOSPHOR BRONZE | GOLD    | 1   |
| 3  | INSULATOR         | DELTRIN         | NATURAL | 1   |
| 2  | HOUSING WITH BODY | BRASS           | NICKEL  | 1   |
| 1  | SHELL             | BRASS           | NICKEL  | 1   |
|    | DESCRIPTION       | MATERIAL        | FINISH  | QTY |

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [ ] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:  
0.5 – 8mm ± 0.20mm  
8 – 30mm ± 0.40mm  
30 – 120mm ± 0.50mm

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:  
.020 – .315 = ± 0.007"  
.315 – 1.180 = ± 0.015"  
1.180 – 4.724 = ± 0.020"

DO NOT SCALE DRAWING

| APPROVALS     | DATE                 |
|---------------|----------------------|
| DRAWN J.CHENG | 05/14/09             |
| CHECKED       |                      |
| ISSUED        |                      |
| SHEET 1 OF 1  |                      |
| CAD FILE      | C:/CONNEX/122153.DWG |

# Amphenol Connex

PART DESCRIPTION

TNC R/A CRIMP PLUG  
(FOR RG-59/U CABLE)

PART NO.

122153

DWG. NO.

122153.DWG

REV. NC

SIZE A

SCALE NA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[122153](#)