





REV.	DATE	DESCRIPTION
NC	04/31/03	INITIAL RELEASE
A	10/27/05	MODIFY - INSULATOR NOW INTERNAL



RECOMMENDED CABLE
STRIPPING DIMS.



NOTE:
1. CONTACT PIN TO SOLDER

8				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex								
7					DRAWN	G.R.S.						10/27/05			
6					CHECKED										
5					ISSUED			PART DESCRIPTION SMA DIRECT SOLDER JACK (FOR .085”, .086” CABLE)							
4	INSULATOR	TEFLON	NATURAL		1	SHEET	1 OF 1								
3	CONTACT PIN	BER. COPPER	GOLD	1			PART NO. 132103								
2	INSULATOR	TEFLON	NATURAL	1											
1	BODY	BRASS	GOLD	1	CAD FILE	C:/132/132103.DWG	DWG. NO.		132103.DWG	REV.	A	SIZE	A	SCALE	NA
	DESCRIPTION	MATERIAL	FINISH	QTY											

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[132103](#)