



REV.	DATE	DESCRIPTION
NC	05/18/03	INITIAL RELEASE



REV.	DATE	DESCRIPTION		
NC	05/18/03	INITIAL RELEASE		
8				
7				
6				
5	HEX NUT	BRASS GOLD 1		
4	LOCK WASHER	BRASS GOLD 1		
3	CONTACT PIN	BRASS GOLD 1		
2	INSULATOR	TEFLON NATURAL 1		
1	HOUSING/BODY	BRASS GOLD 1		
	DESCRIPTION	MATERIAL FINISH QTY		
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.		APPROVALS	DATE	<h1 style="color: blue;">Amphenol Connex</h1>
UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm		DRAWN G.R.S.	05/18/03	
UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020"		CHECKED		
DO NOT SCALE DRAWING		ISSUED		
		SHEET 1 OF 1		
		CAD FILE C:/142/142210-10.DWG		PART DESCRIPTION
				SMB P.C. MOUNT & BULKHEAD JACK (EXTENDED BODY)
				PART NO.
				142210-10
				DWG. NO.
				142210-10.DWG
				REV.
				NC
				SIZE
				A
				SCALE
				NA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[142210-10](#)