



REV.	DATE	DESCRIPTION
NC	10/14/01	INITIAL RELEASE
A	06/30/05	UPDATE DRAWING FORMAT
B	09/18/05	ADD P.C.B. LAYOUT



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex									
7						DRAWN	G.R.S.						09/18/05				
6						CHECKED			PART DESCRIPTION								
5						ISSUED			SMB END LAUNCH RECEPTACLE JACK								
4						SHEET	1 OF 1		PART NO. 142311								
3	CONTACT PIN	BER. COPPER	GOLD	1		CAD FILE		C:/142/142311.DWG		DWG. NO.	142311.DWG	REV.	B	SIZE	A	SCALE	NA
2	INSULATOR	TEFLON	NATURAL	1													
1	BODY	BRASS	GOLD	1													
DESCRIPTION MATERIAL FINISH QTY																	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[142311](#)