


REV.	DATE	DESCRIPTION
NC	03/30/08	INITIAL RELEASE



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex				
8						DRAWN	G.R.S.	03/30/08						
7						CHECKED								
6						ISSUED			PART DESCRIPTION SMA REVERSE POLARITY JACK TO TNC JACK ADAPTER					
5						SHEET	1 OF 1							
4	CONTACT PIN	PHOS. BRONZE	GOLD	1						PART NO. 242107RP-10				
3	INSULATOR	TEFLON	NATURAL	1										
2	BODY	BRASS	NICKEL	1						DWG. NO. 242107RP-10.DWG				
1	BODY	BRASS	NICKEL	1										
DESCRIPTION MATERIAL FINISH QTY					CAD FILE C:/242/242107RP-10.DWG					REV. NC		SIZE A	SCALE NA	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[242107RP-10](#)