


REV.	DATE	DESCRIPTION
A	06/05/03	UPDATE DRAWING FORMAT
B	11/13/06	MODIFY BARREL O.D. TO 2.7mm



RECOMMENDED
CABLE STRIPPING DIM'S

- NOTE:
1. CRIMPED FERRULE HEX CRIMP SIZE .128"
 2. CONTACT PIN TO SOLDER

8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex					
7						DRAWN	G.R.S.	11/13/06							
6	FERRULE	COPPER	GOLD	1		CHECKED				PART DESCRIPTION MCX R/A CRIMP PLUG RG 174/u, 188/u, 316/u CABLE					
5	COVER	BRASS	GOLD	1		ISSUED									
4	INSULATOR	DELRIN	NATURAL	1		SHEET	1 OF 1			PART NO. 252102					
3	CONTACT PIN	BRASS	GOLD	1											
2	INSULATOR	TEFLON	NATURAL	1							DWG. NO. 252102.DWG REV. B SIZE A SCALE NA				
1	BODY	BER. COPPER	GOLD	1											
DESCRIPTION		MATERIAL	FINISH	QTY				CAD FILE C:/252/252102.DWG							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[252102](#)