


REV.	DATE	DESCRIPTION
NC	04/01/98	INITIAL RELEASE
A	11/09/06	UPDATE DRAWING FORMAT



8					<small>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.</small> <small>UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:</small> 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm <small>UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:</small> .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020"	APPROVALS	DATE	<h1 style="color: blue;">Amphenol Connex</h1>		
7				DRAWN		G.R.S.	11/09/06		PART DESCRIPTION BNC PANEL JACK (FOUR HOLE) 50ohm	
6				CHECKED						PART NO. 112290
5				ISSUED						
4					SHEET	1 OF 1				
3	CONTACT PIN	BER. COPPER	GOLD	1	CAD FILE			DWG. NO. 112290.DWG		
2	INSULATOR	TEFLON	NATURAL	1	C:/112/112290.DWG				REV. A	
1	BODY	BRASS	NICKEL	1				SIZE A		
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING			SCALE NA		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[112290](#)