










REV.	DATE	DESCRIPTION
A	05/10/01	MODIFY INSULATOR/CONTACT PIN DIMENSIONS
B	01/30/04	UPDATE DRAWING FORMAT



RECOMMENDED
CABLE STRIPPING DIM'S



NOTE:

1. CRIMPED FERRULE
HEX CRIMP SIZE .128"
2. CONTACT PIN TO SOLDER

						UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.		APPROVALS		DATE		Amphenol Connex			
8	HEAT SHRINK TUBE				1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm		DRAWN	G.R.S.	01/30/04					
7	FERRULE	COPPER	GOLD	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”		CHECKED					PART DESCRIPTION SMA CRIMP JACK (FOR RG-178B/U, 196A/U CABLE)			
6	HEX NUT	BRASS	GOLD	1			ISSUED								
5	BARREL	BRASS	GOLD	1			SHEET	1 OF 1				PART NO. 132279			
4	INSULATOR	TEFLON	NATURAL	1											
3	CONTACT PIN	BER. COPPER	GOLD	1							DWG. NO. 132279.DWG				
2	INSULATOR	TEFLON	NATURAL	1											
1	BODY	BRASS	GOLD	1							REV. B		SIZE A	SCALE NA	
DESCRIPTION		MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING		C:/132/132279.DWG								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[132279](#)