


REV.	DATE	DESCRIPTION
A	12/09/03	UPDATE DRAWING FORMAT



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex							
8						DRAWN	G.R.S.	12/09/03									
7						CHECKED											
6							ISSUED				PART DESCRIPTION						
5	HEX NUT	BRASS	NICKEL	1							SMB BULKHEAD RECESSED RECEPT. JACK						
4	LOCK WASHER	BRASS	NICKEL	1							PART NO.						
3	CONTACT PIN	BRASS	GOLD	1							142156						
2	INSULATOR	TEFLON	NATURAL	1													
1	BODY	BRASS	NICKEL	1				SHEET 1 OF 1									
DESCRIPTION					MATERIAL	FINISH	QTY	CAD FILE		DWG. NO.		REV.	NC	SIZE	A	SCALE	NA
								C:/142/142156.DWG		142156.DWG							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[142156](#)