



4.50 [.177] 8.10 [.319] 5.20 [.205]

RECOMMENDED
CABLE STRIPPING DIM'S



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		<h1>Amphenol Connex</h1>							
8						DRAWN	G.R.S.	04/02/08									
7						CHECKED											
6						ISSUED			PART DESCRIPTION								
5						SHEET	1 OF 1		R/A PCB CABLE TERMINATION (RG-174/U, 188B/U, 179/U, 187A/U, 316/U)								
4										PART NO.							
3	FERRULE	COPPER	GOLD	1						142268							
2	BARREL	BRASS	GOLD	1													
1	BODY	BRASS	GOLD	1													
	DESCRIPTION	MATERIAL	FINISH	QTY	CAD FILE C:/142/142268.DWG				DWG. NO.		142268.DWG	REV.	C	SIZE	A	SCALE	NA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[142268](#)