




REV.	DATE	ECR NO.	DESCRIPTION
NC	01/19/98	—	INITIAL RELEASE
A	06/24/08	100039	UPDATE DRAWING FORMAT



RECOMMENDED CABLE
STRIPPING DIMENSIONS

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	Amphenol Connex					
8						DRAWN	GRS						06/24/08
7						CHECKED							
6					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm	ISSUED							
5						SHEET	1 OF 1		PART DESCRIPTION MCX DIRECT SOLDER JACK (FOR .085”, .086” CABLE)				
4					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”								
3	CONTACT PIN	BER. COPPER	GOLD	1					PART NO. 252131				
2	INSULATOR	PTFE	NATURAL	1									
1	BODY	BRASS	GOLD	1					DWG. NO. 252131.DWG REV. A SIZE A SCALE NA				
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING		CAD FILE C:/252/252131.DWG						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[252131](#)