




DESCRIPTION		
REV.	DATE	
NC	01/21/03	INITIAL RELEASE
A	10/10/05	ADD NOTE: 
B	10/31/05	CHANGE GASKET MATERIAL TO SILICONE



- NOTE:
1. CRIMPED FERRULE
HEX CRIMP SIZE .213"
 2. CRIMPED CONTACT PIN
HEX CRIMP SIZE .068"
 3. MAX. PANEL THICKNESS = 6.5mm
 UL APPROVED.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.		
UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:		
0.5 - 8mm ± 0.20mm	8 - 30mm ± 0.40mm	30 - 120mm ± 0.50mm
UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:		
.020 - .315 ± 0.007"	.315 - 1.180 ± 0.015"	1.180 - 4.724 ± 0.020"
DO NOT SCALE DRAWING		
CAD FILE C:/122/122479.DWG		
DWG. NO. 122479.DWG		
REV. B SIZE A SCALE NA		
PART DESCRIPTION		
TNC BULKHEAD CRIMP JACK (FOR RG-142A/U, 223/U, 400/U CABLE)		
122479		
APPROVALS		
DATE	DATE	DATE
10/31/05	10/31/05	10/31/05
G.R.S.	G.R.S.	G.R.S.
CHECKED	CHECKED	CHECKED
ISSUED	ISSUED	ISSUED
SHEET 1 OF 1	SHEET 1 OF 1	SHEET 1 OF 1
PART NO. 122479		
DESCRIPTION		
16 HEX		
FERRULE		
HEX NUT		
LOCK WASHER		
GASKET		
CONTACT PIN		
INSULATOR		
BODY		
DESCRIPTION		
MATERIAL		
FINISH		
QTY		
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.		
UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:		
0.5 - 8mm ± 0.20mm		
8 - 30mm ± 0.40mm		
30 - 120mm ± 0.50mm		
UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:		
.020 - .315 ± 0.007"		
.315 - 1.180 ± 0.015"		
1.180 - 4.724 ± 0.020"		
DO NOT SCALE DRAWING		
CAD FILE C:/122/122479.DWG		
DWG. NO. 122479.DWG		
REV. B SIZE A SCALE NA		
PART DESCRIPTION		
TNC BULKHEAD CRIMP JACK (FOR RG-142A/U, 223/U, 400/U CABLE)		
122479		
DESCRIPTION		
MATERIAL		
FINISH		
QTY		
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.		
UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:		
0.5 - 8mm ± 0.20mm		
8 - 30mm ± 0.40mm		
30 - 120mm ± 0.50mm		
UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:		
.020 - .315 ± 0.007"		
.315 - 1.180 ± 0.015"		
1.180 - 4.724 ± 0.020"		
DO NOT SCALE DRAWING		
CAD FILE C:/122/122479.DWG		
DWG. NO. 122479.DWG		
REV. B SIZE A SCALE NA		
PART DESCRIPTION		
TNC BULKHEAD CRIMP JACK (FOR RG-142A/U, 223/U, 400/U CABLE)		
122479		
DESCRIPTION		
MATERIAL		
FINISH		
QTY		

Amphenol Connex

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[122479](#)