






REV.	DATE	ECR NO	DESCRIPTION
A	--	--	RELEASE TO MFG.
B	01/10/04	--	UPDATE DRAWING FORMAT/ MODIFY MOUNTING POSTS
C	02/25/10	2012	HARDWARES REMOVED



DETAIL -A-
(2X SCALE)



PCB MOUNTING HOLES



NOTE:
1. MAX. PANEL THICKNESS = 5mm

				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”	APPROVALS	DATE	Amphenol Connex								
					DRAWN	CLEMENT					02/25/10				
					CHECKED			PART DESCRIPTION							
					ISSUED			BNC STRAIGHT PC MOUNT RECEPT. JACK							
					SHEET	1 OF 1		PART NO.							
5	MOUNTING POST	BRASS	TIN PLATING				112495								
4	POST	COPPER	TIN PLATING												
3	CONTACT PIN	PHOS. BRONZE	GOLD												
2	INSULATOR	POLY PRO.	NATURAL												
1	BODY	ZINC DIE CAST	NICKEL												
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	CAD FILE	C:/112/112495.DWG	DWG. NO.	112495.DWG	REV.	C	SIZE	A	SCALE	NA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[112495](#)