


REV.	DATE	ECR NO.	DESCRIPTION
NC	06/05/10	-	INITIAL RELEASE



NOTE:
1. CRIMPED FERRULE
HEX CRIMP SIZE .178"

QTY	DESCRIPTION	MATERIAL	FINISH
1	SHELL	BRASS	NICKEL
2	HOUSING	BRASS	NICKEL
3	BARREL	BRASS	NICKEL
4	INSULATOR	DELTRIN	NATURAL
5	CONTACT PIN	BRASS	GOLD
6	GASKET	RUBBER	RED
7	RETAINER RING	BRASS	NICKEL
8	RING	DELTRIN	NATURAL
9	WASHER	BRASS	NICKEL
10	FERRULE	BRASS	NICKEL
11	NUT	BRASS	NICKEL

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:
0.5 - 8mm ± 0.20 mm
8 - 30mm ± 0.40 mm
30 - 120mm ± 0.50 mm

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:
.020 - .315 ± 0.007 "
.315 - 1.180 ± 0.015 "
1.180 - 4.724 ± 0.020 "

DO NOT SCALE DRAWING

APPROVALS	DATE
DRAWN J.CHENG	06/05/10
CHECKED	
ISSUED	
SHEET 1 OF 1	
CAD FILE	C:/CONNEX/122149.DWG

PART DESCRIPTION			
Amphenol Connex			
TNC R/A CRIMP PLUG (FOR RG-179/U,187A/U CABLE)			
PART NO.		122149	
DWG. NO.	122149.DWG	REV.	NC
SIZE	A	SCALE	NA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[122149](#)