


REV.	DATE	DESCRIPTION
NC	02/05/07	INITIAL RELEASE



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”	APPROVALS		DATE		Amphenol Connex					
8						DRAWN	G.R.S.	02/05/07							
7						CHECKED			PART DESCRIPTION TNC MALE CAP W/CHAIN						
6						ISSUED									
5						SHEET	1 OF 1			PART NO. 202101					
4	RIVET	BRASS	NICKEL	1											
3	CHAIN	BRASS	NICKEL	1					DWG. NO. 202101.DWG						
2	GASKET	SILICONE	RED	1											
1	SHELL/BODY	BRASS	NICKEL	1					REV.		NC	SIZE	A	SCALE	NA
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING		CAD FILE		C:/202/202101.DWG						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[202101](#)