


REV.	DATE	DESCRIPTION
NC	07/14/02	INITIAL RELEASE
A	11/01/05	UPDATE DRAWING FORMAT

5/8-24UNEF-2B (INTERNAL)



QTY	FINISH	MATERIAL	DESCRIPTION
1	NICKEL	BRASS	BODY
1	NATURAL	TEFLON	INSULATOR
1	RED	SILICONE	GASKET

DATE	APPROVALS
11/01/05	G.R.S.

DATE	DESCRIPTION
11/01/05	N PLUG TO TNC REVERSE POLARITY JACK ADAPTOR

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.
TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm	TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020"

DO NOT SCALE DRAWING	CAD FILE C:/242/242130RP.DWG
----------------------	---------------------------------

DWG. NO.	REV.	SIZE	SCALE
242130RP.DWG	A	A	NA

Amphenol Connex

PART NO. 242130RP

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[242130RP](#)