



REV.	DATE	DESCRIPTION
NC	10/31/01	INITIAL RELEASE



DESCRIPTION	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS DIMENSIONS IN [ ] ARE IN INCHES FOR CUSTOMER REFERENCE ONLY		APPROVALS	DATE
1 BODY	BRASS	NICKEL	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5-6 = ± 0.2 6-30 = ± 0.4 30-120 = ± 0.6 120-315 = ± 1 315-1000 = ± 1.6 1000-2000 = ± 2.4		DRAWN G.R.S.	10/31/01
2 INSULATOR	TEFLON	NATURAL			CHECKED	
3 CONTACT PIN	BER COPPER	GOLD			ISSUED	
4						
5						
6						
7						
8			DO NOT SCALE DRAWINGS			

TITLE				
N JACK TO MCX PLUG ADAPTOR				
<div> Connex Connector Corporation</div>				
SIZE	FSDM NO.	DWG. NO.	REV.	
A	99001	242171.DWG	NC	
SCALE	PART NO.	SHEET		
NA	242171	1 OF 1		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[242171](#)