

BergStak® 0.40mm Self-Alignment Board-to-Board Connector

USCAR-2 COMPLIANT CONNECTORS WITH SELF-ALIGNING FEATURE

The BergStak® 0.40mm self-alignment connectors come with a stack height of 3.50mm and 30 positions extendable up to 10 to 60 positions with 10 positions incremental. It has a unique self-alignment feature that supports blind mating, ensuring a reliable connection. The USCAR-2 compliant connector is also ideal for the automotive market.

- 0.40mm fine pitch design
- Self-alignment feature
- Supports speed performance up to 8Gb/s
- Meets USCAR-2 vibration and shock limits



TARGET MARKETS



FEATURES

- Fine pitch design at 0.40mm
- Self-alignment feature
- 3.50mm stack height and 30 positions extendable up to 10 to 60 positions
- Supports speed performance up to 8Gb/s
- Meets USCAR-2 vibration and shock limits
- RoHS compliant, halogen and lead free

BENEFITS

- Suitable for applications with space constraints
- Supports blind mating
- Support different applications
- Meets PCIe® Gen 3 standards
- Suitable for automotive application
- Meets health, safety and environment requirements

TECHNICAL INFORMATION

MATERIAL

- Housing: High temperature thermoplastic LCP, UL94V-0, black
- Terminal: Copper alloy
- Metal Hold-down: Copper alloy
- Plating: Gold

ELECTRICAL PERFORMANCE

- Current Rating per Contact: 0.3A per contact
- Insulation Resistance: 50M Ω min.
- Voltage Rating: 30V AC

MECHANICAL PERFORMANCE

- Durability: 30 mating cycles

ENVIRONMENTAL

- Operating Temperature Range: -40°C to +125°C
- SO2 Gas: Duration 96 hours
- Mechanical Shock and Vibration: Pass USCAR-2 Class V1

SPECIFICATIONS

- Product Specification: GS-12-1404

PACKAGING

- Tape & Reel

TARGET MARKETS/APPLICATIONS



Car camera



Portable IoT devices
Gaming device



Factory automation camera



Patient monitor

PART NUMBERS

Description	Part Numbers
BergStak® 0.40mm self-alignment header, 30 positions, 3.50mm stack height	10142886-030A2EHLF
BergStak® 0.40mm self-alignment receptacle, 30 positions, 3.50mm stack height	10142890-030A3EHLF

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10142886-030A2EHLF](#) [10142890-030A3EHLF](#)