

#### ROHS PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P91C*GL00LF
15	39.14	33.32	25.18	25.12	19.18	D15P91C*GL00LF
25	53.03	47.04	39.12	38.84	33.12	D25P91C*GL00LF
37	69.32	63.50	55.68	55.30	49.68	D37P91C*GL00LF

Plating: 4 --> 200 Mating  
Plating: 6 --> 500 Mating  
Plating: 8 --> 1.25µ Equivalent PdNi/Au


GENERAL CHARACTERISTICS AND ROHS INFORMATION:  
SEE DRAWING C01-8646-0001




#### PC board drilling dimensions(after plating)

(thickness ≤ 3.20±0.30mm)

Pitch 2.76(shell 25-37)

pitch 2.74(shell 09-15)



mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family D-SUB									
ltr	ecn no	dr	date	tolerances unless otherwise specified						title									
L	ELX-I-21654	AB	2015-10-26	angles	linear	.0±0.1				MALE DELTA-D STRAIGHT PRESS-FIT									
M	ELX-I-24020	AAB	2016-06-06			.00±0.1													
						.000±0.1													
				0°±2'		.000±0.1		scale 2:1		dwg no									
				dr	JARRY	1994-09-21			sheet 1 of 1				size						
				engr	MITHUN PAUL	2016-06-06			C01-8646-0311				A3						
				chr	ATHUL A.B	2016-06-06													
				appd	BIJU K PAUL	2016-06-06													
sheet index		revision sheet		M	1														

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[D09P91C4GL00LF](#) [D25P91C4GL00LF](#) [D25P91C6GL00LF](#) [D09P91C4GL00](#) [D15P91C6GL00](#) [D25P91C4GL00](#)  
[D25P91C6GL00](#) [D37P91C4GL00](#) [D15P91C4GL00LF](#)