





FCIconnect.com

Copyright FCI

SINGLE ROW



DOUBLE ROW



ORDERING INFORMATION

8614 - 00 - XX - X - YO - X - XXX - XX

LF :: LEAD FREE

SERIES

OPEN MALE HEADER

NO: OF CONTACTS

01 TO 36 FOR SINGLE ROW
02 TO 72 FOR DOUBLE ROW

NO. OF ROWS

1 - SINGLE ROW
2 - DOUBLE ROW

TYPE OF CONTACT

VERTICAL FLOW SOLDER

SPECIAL CODES

PLATING : NOTE 3

NOTES:

- 1, THE REMAINING AREA ON THE CONTACT SIDE FOLLOWING THE DIMENSION 'T' SHOULD BE PLATED WITH GOLD FLASH
- 2, THE PRODUCT (LF) MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-47-004
3. FOR PLATING DETAILS AND TECHNICAL SPECIFICATION REFER DRAWING : C-8614-0000

13	8614-00-XX-X-YO-X-313	4.5	21.0	5.7	12.76
12	8614-00-XX-X-YO-X-314	5.8	19.6	7.0	10.06
11	8614-00-XX-X-YO-X-315	4.5	18.3	5.7	10.06
10	8614-00-XX-X-YO-X-316	4.5	15.8	5.7	7.56
09	8614-00-XX-X-YO-X-317	4.8	13.5	6.0	4.96
08	8614-00-XX-X-YO-X-318	14.2	21.0	15.4	3.06
07	8614-00-XX-X-YO-X-319	4.6	11.9	5.8	3.46
06	8614-00-XX-X-YO-X-320	4.2	18.3	12.7	3.06
05	8614-00-XX-X-YO-X-321	5.5	12.5	6.7	3.26
04	8614-00-XX-X-YO-X-322	5.8	12.5	7.0	2.96
03	8614-00-XX-X-YO-X-323	4.6	11.3	5.8	2.96
02	8614-00-XX-X-YO-X-324	7.3	13.5	8.5	2.46
01	8614-00-XX-X-YO-X-325	4.5	10.8	5.7	2.56
SL No.	OEN PART NO:	T	L±0.3	Y±0.2	Z±0.2
		DIMENSIONS			

mat'l. code NOTE 3				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection MM	product family 8614			
ltr	ecn no	dr	date	tolerances unless otherwise specified		MM	title 8614 OPEN HEADER (STRAIGHT SPILL)			
A	106-0179	AB	2006-08-29	angles	linear					
B	108-0006	MINI	2008-01-17	±1°		scale —	dwg no C-8614-0127			
C	109-0184	GT	2009-09-05							
D	110-0077	GT	2010-03-22	dr	MINI K V	2003-05-02	sheet 1 of 1			
E	110-0136	GT	2010-06-23	enrg	GEORGE V JOSEPH	2003-05-02				
F	ELX-1-16863	GM	2014-01-27	chr	GREGAR.MATHEW	2013-02-05	A3			
				appd	BIJU K PAUL	2013-02-05				
sheet index		revision sheet	E 1							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[861400071YO15320](#) [861400071YO15320LF](#) [861400102YO9323](#) [861400102YO9323LF](#) [861400202YO15320](#)
[861400361YO2319](#) [861400402YO2319](#) [861400031YO1](#) [861400031YO2319LF](#) [861400051YO2319LF](#)
[861400042YO2319LF](#)