






Copyright FCI.

A


B

C

D



LAYOUT FOR P.C.B
scale : 2.5



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE GS-12-447

NOTE-2: COMPATIBLE WITH NARROW AND WIDE BODY

NOTE-3: PCB FINISH HOLE DIAMETER : SEE GS-12-447

NOTE-4: STANDARD PACKAGING IS IN TUBE ,BUT IF SUFFIX "P"
IS ADDED IN P/N ,PACKAGING IS IN TRAYS ,BUT CONNECTOR
MARKING IS WITHOUT "P"
Example: HM1FxxxxxxxH6PLF, marking: HM1FxxxxxxxH6LF

SPECIFIC DATAS:

Visual inspection : 100%

- Marking failures
- Housing material failures
- Spoilt housing
- Stained housing
- Broken contacts (twisted or loosen)

△ PART NUMBER

HM1S41FER400H*(LF)

LF = FOR LEAD FREE PRODUCT

PLATING CODE:




6 = TELCORDIA CO

E = CUSTOMER SPECIAL, CONTACT

30u" GOLD SELECTIVE PLATING.

European Views

rev	ecn no	dr	date
A	-	-	2001/01/26
B	LS05-004	MLE	2005/02/22
C	LS06-0095	LGO	2006/07/05
D	LS06-0159	MLE	2006/10/24
E	LS07-0266	MLE	2007/11/09
F	DG09-0367	TER	2009-11-25
-	-	-	-

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 					
			TOLERANCES UNLESS OTHERWISE SPECIFIED											
Dr	PERRICHOT	2001/01/26	ANGULAR		LINEAR		0.X	±0.1	size	A3	Scale	4		
Eng	LENOIR	2001/01/26	0.XX ±2				0.XX	±0.1	ECN DG09-0367					
Chr	LEGARE	2001/01/26					0.XXX	±0.1						
Appr	LEGARE	2001/01/26	Product family					METRAL		Spec ref -				
		title	METRAL FEM. 4 ROW STRAIGHT PRESS FIT					dwg no	C-8626-11110			Rev	F	
			PCB THICKNESS 2.4 mm MINIMUM											
			catalog no											-
			CUSTOMER											sheet 1 of 1

REV F - 2006-04-17

1

2

3

PDM: Rev:F

STATUS:Released

4

Printed: Jan 13, 2010

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[HM1S41FER400HEPLF](#)