





Amphenol PCD SZ
ORIGINAL
PDF Format
R&D

安费诺精密连接器(深圳)有限公司
Amphenol PCD Shenzhen

受控文件
2018年10月11日



SECTION A-A



SCALE 4:1

✦: IS CRITICAL CHARACTERISTIC SYMBOL, ◎: IS IMPORTANT CHARACTERISTIC SYMBOL.

NOTES:

- ✦ 1. MATERIAL: CONTACT BODY: COPPER ALLOY; T=0.3mm,
CLIP: STAINLESS STEEL, T=0.15mm.
2. CONTACT BODY PLATING: TIN PLATING.
- ◎ 3. WIRE RANGE: 18~14AWG(0.75~2.0 SQ MM),
WIRE INSULATION OD RANGE: FROM 2.2MM TO 3.0MM.
- ✦ 4. ROHS COMPLIANCE.
5. REEL PACKING 3000PCS PER REEL.

DIMENSIONS	TOLERANCES	PROJECTION	Amphenol Pcd Shenzhen		TITLE				
ANSI Y14.5M	.X ±0.5		ENGR		FEMALE CONTACT Ø1.6				
UNITS: MM	.XX ±0.05		LUIK.PENG Mar-23-18		FOR 0.75~2.0MM^2				
Pro/E FILE	ANGLES ±3.0°								
ORIGINAL	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD SHENZHEN		CHKD		SIZE	DWG NO.	REV		
			APPD		A3	C-LVRC16PC01S		A	
			CODE: 58982		SCALE: 6:1	SHEET 1 OF 1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[LVRC16PC01S](#)