

Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	TPU, UL 94
Coupling screw:	CuZn, nickel plated
Moulding body:	TPU, UL 94, grey

PE green-yellow

2 brown


3 blue

Part no:	Description:	Length L:	Cable:
41-01028	SAL - 7/8 - RSW2PE - 2 / K0	2m	TPU, UL 20940, black, 3x0,75mm² Cable: 781-K07300
41-01029	SAL - 7/8 - RSW2PE - 3 / K0	3m	
41-01030	SAL - 7/8 - RSW2PE - 5 / K0	5m	
41-01031	SAL - 7/8 - RSW2PE - 10 / K0	10m	
41-xxxxx	SAL - 7/8 - RSW2PE - ... / K0	x	
41-01125	SAL - 7/8 - RSW2PE - 2 / K0 / 150	2m	TPU, UL 20940, black, 3x1,50mm² Cable: 781-K08300
41-01126	SAL - 7/8 - RSW2PE - 3 / K0 / 150	3m	
41-01127	SAL - 7/8 - RSW2PE - 5 / K0 / 150	5m	
41-01128	SAL - 7/8 - RSW2PE - 10 / K0 / 150	10m	
41-xxxxx	SAL - 7/8 - RSW2PE - ... / K0 / 150	x	

D see data sheet cable

IDO NOT ALTER CAD DRAWING BY HAND

Directive 2002/95/EC RoHS compliant

Index: b 14.02.11 VF Å3891 cable type changed, technical specification changed, part no. cable in table added, neutral line added	dim. in mm			title: Male connector 7/8" angled
	date	name		
tolerance of cable: L <= 4m: L + 40mm L > 4m: L + 1%	drawn	11.10.07	Franz	dwg no: 41K1A312
	appd.	11.10.07	Mankopf	
general tolerance: 0 ± 0,50mm 0,0 ± 0,25mm 0,00 ± 0,10mm				part no: see table
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH.				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[41-01128](#)