



Technical specification:

Rated voltage: IEC 61076-2-101	60 V
Current rating: IEC 61076-2-101	4 A bei 40°C
Insulation resistance: IEC 60512-2	$\geq 100 \text{ M}\Omega$
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 67, in mated condition
Temperature range: IEC 60664-1	-25°C ... +85°C
Mating cycles: IEC 60512-9a	≥ 100


Materials:

Contact:	CuSn
Contact plating:	Nickel, gold plated
Contact carrier:	TPU
Moulding body:	TPU, RAL 7001
Sealing:	FPM


Installation specification:

Recommended torque:	0,6 Nm
---------------------	--------

Contact assignment:



Part no:	Description:
43-05101	SAL - 12 - RS5 - 2RK5.2

DO NOT ALTER CAD DRAWING BY HAND Directive 2002/95/EC RoHS compliant	Index: a 24.08.11 VF Ä3941 data sheet revised		 dim. in mm		title: Junction box, male connector M12x1 - 2x female connector M12x1	
			date	name		
	tolerance of cable:		drawn	05.04.07	Franz	dwg no:
			appd.	08.04.07	Mankopf	
	general tolerance:				43K1A488	
0 ± 0,50mm 0,0 ± 0,25mm 0,00 ± 0,10mm						
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				part no: see table		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[43-05101](#)