



used for: D-SUB

9pos.



15-50pos.



(b)

No. of pos.	A	B	C	D	ØE	Part-No.
9	32.0	25.00	55.0	14.8	12.1	165X11159X
15	39.3	33.30	55.0	14.8	12.1	165X10869X
25	53.2	47.04	55.0	14.8	12.1	165X10879X
37	69.5	63.50	55.0	14.8	12.1	165X10889X
50	67.0	61.10	55.0	17.8	14.6	165X10899X

(c) Delivery includes:

Hood with cover

Blanking plug:

- 9pos.: with 1 blanking plug
- 15-50pos.: with 2 blanking plugs

Screws for fixing:

- 9pos.: with 3 screws
- 15-50pos.: with 4 screws

1 earth screw

(d) 2 mounting screws for connector

RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

				tolerance		 dim. in mm
				2005	date	
				drawn	18.10.	Lehmenkühler
				appd.	19.10.	Mickenbecker
3 x d	Ä20-0033	10.02.20	Lehm.	norm		
1 x c	Ä4037	19.07.11	Lehm.	d-old		
1 x b	Ä3264	29.01.09	Sonne			
a	Original					
rev.	description	date	name			

scale:	1:1
material:	HOOD WITH COVER: DIE-CAST ZINC
title:	METAL HOOD EMI/RFI SHIELDING 9-50pos.
dwg no:	16K1A1526
part no:	SEE TABLE
DIN-A	3
sh:	1/1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[165X11159X](#)