




NOTES:

- METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
- INSULATORS: PBT GF UL 94 V-0; GREEN
- SIGNAL CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
SOLDER CUP ACCEPTS CABLE AWG 20
- NO CONTACT ON POS. A1
- CONNECTOR IS PART MARKED: 3021W1PAM99A10X CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH										
DO NOT ALTER CAD DRAWING BY HAND				tolerance		 dim. in mm	scale: 2:1 (5:1)			
							material: SEE NOTES			
								title: D-SUB COMBINATION MALE 21W1P SOLDER CUP		
				date	name	dwg no: 13K1A4333 part no: 3021W1PAM99A10X				
				drawn	27.05.13					Henneboel
				appd.	27.05.13					Koch
				norm						
				d-old		DIN-A3 sh: 1				
a	Original									
rev.	description	date	name							

DIN-A3
sh: 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[3021W1PAM99A10X](#)