






NOTES:

- METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
- INSULATORS: PBT GF UL 94 V-0, GREEN
- SIGNAL CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
- NO CONTACTS ON POS. A1 + A2
- P.C.B. HOLE DRILLINGS SEE SHEET 2
- CONNECTOR IS PART MARKED: 3027W2SAR99A10X CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance		 dim. in mm	scale: 2:1 (5:1)					
							material: SEE NOTES					
									date	name	title: D-SUB COMBINATION FEMALE 27W2S	
								drawn	02.05.14	Henneboel		
								appd.	02.05.14	Schmidt		
								norm				
				d-old			dwg no:					
						13K1A4667		DIN-A3				
a	Original					sh: 1/2						
rev.	description	date	name			part no:		3027W2SAR99A10X				

P.C.B. HOLE DRILLINGS
(P.C.B. TOP SIDE)



THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH	DO NOT ALTER CAD DRAWING BY HAND				tolerance		 dim. in mm	scale: 2:1		
								material: SEE SHEET 1		
					date	name		title: P.C.B. HOLE DRILLINGS D-SUB COMBINATION FEMALE 27W2S		
					drawn	02.05.14	Henneboel			
					appd.	02.05.14	Schmidt			
					norm					
					d-old				dwg no: 13K1A4667	
		a	Original							DIN-A3
		rev.	description	date	name			part no: SEE SHEET 1		sh: 2/2

CONEC®

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[3027W2SAR99A10X](#)