









(5:1)



NOTES:

- METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
- INSULATORS: PBT GF UL 94 V-0; GREEN
- SIGNAL CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
- NO CONTACTS ON POS. A1 - A2
- CONNECTOR IS PART MARKED: 3017W2PAR99A10X CONEC ABC

RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH					tolerance		 dim. in mm	scale: 2:1 (5:1)		
								material: SEE NOTES		
						date	name	title: D-SUB COMBINATION MALE 17W2P		
					drawn	14.09.15	Henneboel			
					appd.	14.09.15	Lehmenkühler			
					norm					
					d-old			dwg no: 13K1A5048 part no: 3017W2PAR99A10X		
										DIN-A3 sh: 1
	a	Original								
	rev.	description	date	name						

CONEC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[3017W2PAR99A10X](#)