

D-SUB STANDARD

Interface adapter – Gender Changer – Configuration of contacts 1:1




RoHS compliant – CSA listed, File No.: LR 115000-1 – UL listed, File No.: E202784

DESCRIPTION


- Variation plug to plug and socket to socket
- Stamped contacts
- 4-40 UNC threaded lock
- Quality class 3 (other quality classes on request)
- Shell: Steel tin plated

PRODUCT DRAWING


Variation socket to socket




No. of pos.	A -0.76	B -0.25	C
09	31.19	16.46	25.00 ±0.12
15	39.52	24.79	33.30 ±0.15 ±0.10
25	53.42	38.50	47.04 ±0.13
37	69.70	54.96	63.50 ±0.13



Variation plug to plug



No. of pos.	A -0.76	B +0.25	C	D -0.30
09	31.19	16.79	25.00 ±0.12	16.46
15	39.52	25.12	33.30 ±0.15 ±0.10	24.79
25	53.42	38.84	47.04 ±0.13	38.50
37	69.70	55.30	63.50 ±0.13	54.96



ORDER DATA

SOCKET CONNECTOR – SOCKET CONNECTOR		
No. of pos.	Mounting style 4-40 UNC	Part Number
09	Threaded lock	320X 12519 X
15	Threaded lock	320X 12539 X
25	Threaded lock	320X 10559 X
37	Threaded lock	320X 12559 X

PLUG CONNECTOR – PLUG CONNECTOR		
No. of pos.	Mounting style 4-40 UNC	Part Number
09	Threaded lock	320X 12509 X
15	Threaded lock	320X 12529 X
25	Threaded lock	320X 10549 X
37	Threaded lock	320X 12549 X

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[320X10549X](#) [320X10559X](#) [320X12509X](#) [320X12519X](#) [320X12539X](#) [320X12549X](#) [320X12559X](#)