







SEE NOTE 4



Directive 2002/95/EC
"RoHS"
Compliant

APPROVAL # FREIGABE # DEBLOCKAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCKAGE # AUTORIZACION # APPROVAL	

NOTES:

- METALSHELLS: COPPER ALLOY; min. 315µin TIN over 40-80µin NICKEL
- INSULATORS: PBT GF UL 94 V-0, BLACK
- CONTACTS: COPPER ALLOY
PLATING: 8µin HARD GOLD over min. 50µin NICKEL
SOLDER CUP ACCEPTS CABLE AWG 20
- CONNECTOR IS PART MARKED: DSSNXSMAD01X CONEC ABC

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance				dim. in mm		scale: 2:1	
										material: SEE NOTES	
										title: D-SUB FEMALE 9pos. SOLDER CUP	
										dwg no: 16K1A2449	
DO NOT ALTER CAD DRAWING BY HAND				date				name		Inventor	
				drawn 10.02.09				Petker		DIN-A4	
				appd. 10.02.09				Fischer		sh: 1	
				norm DIN 41652							
				d-old							
a Origin				CONEC							
rev. description date name										part no: DSSNXSMAD01X	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[DSSNXSMAD01X](#)