

4


3

2


1

used for:


D-SUB



Wire size AWG	Crimp height A
24	0,68 - 0,86
22	0,68 - 0,86
20	0,68 - 0,86



STRIPPING DIMENSIONS



Finish

Part-N0.

8µ" hard-gold-plated in the contact area	163A20679X
30µ" hard-gold-plated in the contact area	163C20679X

NOTES:

Material: phosphor bronze

Finish: see table

Temperature range: -55°C to +125°C

Rated current: 7.5A

Contact resistance: ≤ 10mOhm

Crimping: use crimp tool 360X10079X

APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL	

Directive 2002/95/EC
"RoHS"
Compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

				tolerance			dim. in mm
rev.	description	date	name	2005	date	name	
				drawn	07.04.	Lehmenkühler	
				appd.	07.04.	Mickenbecker	
				norm			
				d-old			
				CONEC®			

scale:	5:1
material:	SEE NOTES
title:	PLUG CONTACT CRIMP AWG24-20 (separate contacts)
dwg no:	AutoCAD 2004
part no:	16K1A1363
	SEE TABLE

4

3

2

1

DIN-A
4
sh: 1/1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[163A20679X](#)