


D-SUB HIGH DENSITY

Solder pin – Angled – .350"/7.98 mm – Stamped contacts – Plastic bracket




RoHS compliant – CSA listed, File No.: LR 115000-1 – UL listed, File No.: E202784


SOCKET CONNECTOR




No. of pos.	A -0.76	B +0.25	C
15	31.19	16.46	25.00 +0.12
26	39.52	24.79	33.30 +0.15
44	53.42	38.50	47.04 +0.13
62	69.70	54.96	63.50 +0.13
78	67.31	52.55	61.10 +0.16



15-62 pos.




78 pos.




DESCRIPTION

- Mounting styles:
 - with mounting bracket, PCB clip and 4-40 UNC hex bolt
 - with mounting bracket, PCB clip and 4-40 UNC threaded insert
- Quality class 3 (other quality classes on request)
- Shell: Steel tin plated


PLUG CONNECTOR




No. of pos.	A -0.76	B +0.25	C	D -0.3
15	31.19	16.79	25.00 +0.12	6.12
26	39.52	25.12	33.30 +0.15	6.12
44	53.42	38.84	47.04 +0.13	5.99
62	69.70	55.30	63.50 +0.13	5.99
78	67.31	52.68	61.10 +0.16	5.99



15-62 pos.



78 pos.



ORDER DATA

SOCKET CONNECTOR		
No. of pos.	Mounting style 4-40 UNC	Part Number
15	PCB clip / Hex bolt	302 A 10869 X
26	PCB clip / Hex bolt	302 A 10879 X
44	PCB clip / Hex bolt	302 A 10889 X
62	PCB clip / Hex bolt	302 A 10899 X
78	PCB clip / Hex bolt	302 A 11629 X

PLUG CONNECTOR		
No. of pos.	Mounting style 4-40 UNC	Part Number
15	PCB clip / Hex bolt	301 A 10869 X
26	PCB clip / Hex bolt	301 A 10879 X
44	PCB clip / Hex bolt	301 A 10889 X
62	PCB clip / Hex bolt	301 A 10899 X
78	PCB clip / Hex bolt	301 A 11369 X

SOCKET CONNECTOR		
No. of pos.	Mounting style 4-40 UNC	Part Number
15	PCB clip / Threaded insert	DLH 1XS 8 AK53 X
26	PCB clip / Threaded insert	DLH 2XS 8 AK53 X
44	PCB clip / Threaded insert	DLH 3XS 8 AK53 X
62	PCB clip / Threaded insert	DLH 4XS 8 AK53 X
78	PCB clip / Threaded insert	DLH 5XS 8 AK53 X

PLUG CONNECTOR		
No. of pos.	Mounting style 4-40 UNC	Part Number
15	PCB clip / Threaded insert	DLH 1XP 8 AK53 X
26	PCB clip / Threaded insert	DLH 2XP 8 AK53 X
44	PCB clip / Threaded insert	DLH 3XP 8 AK53 X
62	PCB clip / Threaded insert	DLH 4XP 8 AK53 X
78	PCB clip / Threaded insert	DLH 5XP 8 AK53 X

PCB clip .122"/3.1 ± .004"/0.10 mm hole diameter and .063"/1.6 mm circuit board thickness

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[302A10879X](#)