

Dimension L&B

DIM B	(N-1)×15.0
DIM L	(N-1)×15.0+16

N=Number of poles

Poles	L&B Tolerance
1P-2P	±0.30
3P-4P	±0.50
5P-10P	±0.80

SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item 1 Terminal housing :Thermoplastic (UL 94V-0)
- Item 2 Clamp : Steel Stamping , Zinc plated
- Item 3 Wire guard solder pin : Copper , Tin plated
- Item 4 Terminal screw: Zinc plating"-slot type

Electrical

- Voltage rating: 600V
- Current rating: 127A
- Wire range:
- Solid wire(AWG): 1-20
- Stranded wire(AWG): 1-20
- Torque(Lb-In): 36.5
- Screw: M6
- Wire strip length: 19-20mm
- Withstanding Voltage: 2.2KV
- Operating temperature: -40° C to +115° C
- Soldering temperature: 260° C±5° C/5 Sec
- Safety Approval:
- Critical dimension:

K9 xx C 1 x 3 0 xxx G

- 01 1 POLES
- 02 2 POLES
- 03 3 POLES
-
- 10 10 POLES

COLOR
0 BLACK
5 Green
(RAL6018/T)
6 Blue
8 Grey
(RAL7035/D)
C Green
(RAL6018/U)


000:"@Logo (Standard)
00A:"ANYTEK"Logo
Any special item by
customer request,
please contact sales
department.

G RoHS compliant
(lead<4%)
In copper Alloy

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		K9 15.0 Series without flange (Double-handed)						
PART NO.		K9XXC1X30xxxG			DWG NO.		8K90005	
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance	
			Guoxue 2013.03.06	Guoxue 2013.03.06			UNIT: mm	X. ±0.50
					SCALE: NONE			X.X ±0.30
					SHEET: 01/01		REV: A1	X.XX ±0.10
								X* ±1*

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[K903C1030000G](#) [K905C1030000G](#)