






THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.

Customer Drawing



6		7		8	
REV		ZONE		ECO	
DESCRIPTION		DATE		BY	
A		--		--	
B		--		--	
C		--		--	



- 注 (NOTES):
1. 对配公端直径 Mating contact diameter:1.0mm
 2. 额定电流 Current rating: 5A
 3. 端子类型 Terminatin type: Crimp
 4. 压线规格 Wire size :AWG20~22
 5. 电镀信息 Plating specification:
镍底镀锡 Tin over nickel
 6. 材料规格 Material specification:
6.1. 端子: 铜合金
Contact body: Copper alloy
6.2. 外套: 不锈钢
Outer spring: Stainless steel
 7. 符合ROHS
ROHS compliant

AMPHENOL		Amphenol Technical Products International GZ					
第三角投影 THIRD ANGLE PROJECTION		页面 SHEET	幅面 SIZE	版次 REV.	比例 SCALE	PART NAME:	
1 OF 1		A3	C			HC Contact 20#Socket AWC20~22	
签名 SIGNATURE		日期 DATE		UNLESS OTHERWISE SPECIFIED		DWG NO:	
制图 DRAWN		JS		05/12/20		HCTF12104	
审核 CHECKED		YM		05/12/20		CUST PART #:	
批准 APPROVAL		JL		05/12/20		N/A	
						CUST REV.	
						-	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[HCTF12104](#)